**Technical datasheet** 

## Flexam SW120 01+07 white FG

Article code: SBAS589566



General information	
Product group	Synthetic Belts
Industry segment	Logistics: Distribution & warehousing
Main product feature	Impact resistant, Low friction back side, Foodgrade
Indication of use	Flat, Slider bed, Rollers

Belt construction			
Tension layer	polyester spun, flexible		
Number of plies		1	
Top side	material	Flexam, PVC	
	finish	smooth, glossy	
	color	white	
Bottom side	material	Flexam, PVC	
	finish	impregnated fabric	
	color	white	

Characteristics		
Food Grade (FG)	yes	FDA
Antistatic (AS)	no	
High conductive (HC)	no	
Flame-retardant	no	
	yes	ASTM D-378
ATEX approval	no	

Technical data						
Hardness	ISO 868	top side	80A	Shore		
Force at 1% elongation (static)	ISO 21181		14	N/mm	79.94	lbs/in.
Thickness	AB method KV.002	total	3.20	mm	0.13	in.
		top cover	0.70	mm	0.03	in.
Weight	AB method KV.004		3.8	kg/m²	0.78	lbs/ft²
Coefficient of friction	bottom against steel	dynamic	0.3			
		static	0.4			
Operating temperature	continuous	from / to	-10 / 100	°C	14 / 212	°F
	short	from / to	-10 / 80	°C	14 / 176	°F
Minimum pulley diameter	flexing		50	mm	1.97	in.
	backflexing		75	mm	2.95	in.
Manufacturing width	standard		2000	mm	78.74	in.
	maximum		2000	mm	78.74	in.

## **Fabrication**

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive. For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the seperate information.

## **Additional information**

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F), unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.

Page:2 / 2